# Rapid and simple measurement of grain moisture

# HElite



Handy moisture meter, accurate and reliable during harvesting, drying and storing.

■ Pfeuffer GmbH P.O. Box 248 D-97305 Kitzingen

■ Phone +49-9321-9369-0 Fax +49-9321-9369-50 e-mail info@pfeuffer.com



# Sturdy moisture meter for agriculture



Application and Use

this function.

The moisture content is decisively

significant for the determination of the

correct harvesting moment. The HE

lite has been especially designed for

It is used for the control of the moisture on the field during the threshing process

and for checking the moisture absorp-

The **HE** lite is used for the regular

moisture measurement during the dry-

ing process and during the storage to

tion inside the combine-harvester.

avoid losses in quality.

The **HE** lite is suitable for the moisture determination of cereals, oilseeds and humid maize.

#### **■** Principle of Measurement

The **HE** lite measures the conductivity as well as the temperature of a ground sample. The exact moisture value is calculated by means of an advanced measurement technique. The integrated measurement cell of the HE lite

is based upon the Pfeuffer-principle

proven for more than 40 years: the sample is ground and at the same time homogenized by means of special grinding discs. This guarantees a high reliability of

the HE lite for freshly harvested grain.

#### Measurement

The sample is poured into the filling measure which is integrated in the top unit of the measuring cell and then filled into the grinding chamber. The top unit is placed on to the instrument and screwed down until the limit stop. If required, additionally a ratchet, available as option, can be used. Then the instrument is switched on, the product is selected and the measurement is activated. After some seconds the measuring result appears on the display.

#### **■ Menu Operation**

The menu operation of the HE lite is very simple. The possible options are indicated in the bottom section of the display and are selected by means of three functional buttons. The operation of the instrument is very simple due to the clear and logical menu structure. The trilinear illuminated display is contrasty and highly readable also during absence of light. All information are indicated in plain text.

#### Adjustment of **Calibrations**

If necessary, the HE lite can be calibrated individually by the user. The measured values of each product can be changed by a constant value and a multiplicative factor. This allows an optimal adaptation of the HE lite to individual requirements.

### ■ Calculation of Average Readings

The **HE** lite calculates automatically the average reading of several measurements. Simply select the number of measurements and the indicated measurement readings in the menu "settings" under item "average reading". The average and the single readings are then clearly indicated in the display after each measurement.

## **■** Measuring ranges

wheat, rye, barley,	
oats, triticale	9 - 35 %
rape	5 - 25 %
maize	8 - 45 %
sunflower seeds	5 - 25 %

#### **■ Technical Data**

power supply: 3 x 1.5 V batteries dimensions:

instrument: 200 x 82 x 85 mm 275 x 230 x 83 mm case:

weight: approx. 1.4 kg



We reserve the right to make technical modifications!



Bestepe Mah. Nergiz Sok. No: 7/2 Via Flat İş Mrk. Kat:3 No:87 Yenimahalle - Ankara

Tel: +90 312 248 1351 Fax: +90 312 219 0562

M: +90 532 409 3958

e-mail: serdar@pfeuffer.com.tr

