


★ **Robustness**




	W	L	H
ADF	1200 mm	1200 mm	3500 mm


Automatic Desiccant Filling Machine, fills both sides of the spacer frame simultaneously.

Key Features


	Spacer hickness	Min. Spacer Dimension	Max. Working Height	Silicagel Diameter
ADF2500	6-30 mm	250x250 mm	2800 mm	0,5 - 0,8 mm

System Configuration

 Full Automatic Filling

 Automatic Drilling & Sealing

 PLC Control

 Adjustable Working Height

 Butyl Tank

Desiccant Filling Procedures Under Your Control

With our high technology, innovative and ergonomic control panel, all your dehumidifier filling processes take place automatically under your control. Software designed with a user-friendly interface minimizes operator intervention and shorten the process of all desiccant filling processes and offer you the fastest solution.



Material Tank

We constantly monitor the level of dehumidifier material in the material tank and provide you with a flow of information about the condition of the material. With the electric heating system, we keep your dehumidifier material warm and ready for use..

Remote Access

Remote access feature provides advanced online assistance and troubleshooting



Fill Rate Detection

Excess desiccants are collected with our unit to prevent waste. Collected dehumidifiers are re-used for filling.