



KNF LIQUID PUMPS PRODUCT RANGE



YOUR PARTNER TODAY AND IN THE FUTURE

The KNF Group was founded 1946 in Freiburg, Germany, and is still family-owned. It develops, produces and distributes high-quality diaphragm pumps and systems for gases, vapors and liquids. KNF's innovative diaphragm pumps are available as integrated pumps for OEMs, as well as for process applications and laboratory use. The independent KNF Group has a workforce of 850 employees. Today it comprises 16 companies with five production facilities around the world.

EXPERTS FOR DIAPHRAGM LIQUID PUMPS

KNF Flodos, based in Switzerland, is the KNF Group's product center for liquid pumps. Since its foundation in 1987, KNF Flodos has been focussing on the development and production of diaphragm pumps for the transfer of liquids. These are sold worldwide through the KNF Group's sales organizations. A highly innovative technology leader in its field, KNF Flodos employs some 190 people. The company is very successful in the medical field, laboratory analysis, the inkjet industry and in other high-tech markets.

A KEY COMPONENT IN HIGH-TECH APPLICATIONS

Our customized diaphragm liquid pumps and systems are used in numerous demanding applications. The catalog of industries we serve and applications we support is expanding day by day.

OEM PUMPS

- Inkjet printing
- Medical
- Cleaning and disinfection
- Analytical instruments
- Agriculture
- Chemical processes
- Environmental analysis
- Food
- Fuel cells
- Semiconductors


LABORATORY PUMPS

- Filtration
- Fluid aspiration
- Transfer of liquids
- Dosing of liquids
- Handling of aggressive liquids

KNF MODULAR SYSTEM

MECHANICAL OPTIONS




Connectors



MATERIAL OPTIONS




Valve/diaphragm

Pump head



MOTOR OPTIONS

All common voltage
configurations are available.
Explosion-proof options



OEM PUMPS

- Self priming
- Dry-run safe
- High chemical resistance
- High reliability
- Long life-time
- Low maintenance



NSF National Sanitary Foundation

This label shows that these pumps can be certified for the use with food/consumables.



Digital customization

Thanks to digital technology, this pump can be quickly adapted to the customer's system. This is done by parametrizing the firmware of the motor at KNF.


SINGLE HEADED TRANSFER PUMPS

Type		Flow rate at atmos. pressure (l/min)	Suction height (mWg)	Max. pressure (bar)
NF 5		0.07	3.0	1
FF 12		0.15	3.0	1
FF 20		0.23	3.5	3
NF 25		0.25	3.0	1
NF 30 / NF 30.27*		0.3	6.0	1
NF 60		0.6	3.0	1
NF 100 / NF 100.27*		1.2	3.0	1
NF 300 / NF 300.27*		3.0	3.0	1



DOUBLE HEADED TRANSFER PUMPS

Type		Flow rate at atmos. pressure (l/min)	Suction height (mWg)	Max. pressure (bar)
NFB 5		2 x 0.05	3.0	1
NFB 25		2 x 0.3	3.0	1
NFB 30		2 x 0.3	6.0	1
NFB 60		2 x 0.6	3.0	1
NFB 100		2 x 1.3	3.0	1



SMOOTH FLOW PUMPS

Type		Flow rate at atmos. pressure (l/min)	Suction height (mWg)	Max. pressure (bar)
FP 70		0.7	3.0	2
FP 150		1.5	3.0	2
FP 400		4.6	3.0	1
FP 1.150		1.1	2.3	6
FP 1.400		4.4	3.0	6
NF 600		6.0	3.0	1
FK 1100		12.4	4.5	1



PRESSURE PUMPS FOR UP TO 6 BAR

Type		Flow rate at atmos. pressure (l/min)	Suction height (mWg)	Max. pressure (bar)
NF 1.5		0.06	3.0	6
NF 1.10		0.14	3.0	6
NF 1.25		0.30	3.0	6
NF 1.30		0.17	5.0	6
NF 1.60		0.65	3.0	6
NF 1.100 / NF 1.100.27*		1.2	3.0	6
FP 1.150		1.1	2.3	6
NF 1.300 / NF 1.300.27*		3.0	3.0	6
FP 1.400		4.4	3.0	6
NF 1.600		6.0	3.0	6
FK 1.1100		12.4	4.5	6



* .27: with integrated pressure safety valve

PRESSURE PUMP FOR UP TO 16 BAR

Type	Flow rate at atmos. pressure (l/min)	Suction height (mWg)	Max. pressure (bar)
NF 2.35 	0.35	3.0	16



TRANSFER PUMPS WITH LINEAR DRIVE

Type	Flow rate at atmos. pressure (l/min)	Suction height (mWg)	Max. press. (bar)	Max. frequency (Hz)
FMM 20	0.018	3.0	1	20
FMM 80	0.048	4.0	1	10
FL 10 	0.1	2.0	1	50




DOSING PUMPS WITH TWO-PHASE STEPPER MOTOR

Type	Dispense volume (ml/min)	Suction height (mWg)	Max. pressure (bar)
FEM 1.02	0.2 – 20	4.0	6
FEM 1.09	0.9 – 90	4.0	6




DOSING SYSTEMS WITH TWO-PHASE STEPPER MOTOR

Type	Dispense volume (µl)	Suction height (mWg)	Max. pressure (bar)
FEM 1.02.55 RC	5 – 180	4.0	6
FEM 1.09.55 RC	10 – 520	4.0	6



EXPLOSION-PROOF PUMPS

- ATEX certified
- For use in hazardous locations
- For transfer of flammable liquids
- Available with pressure safety valve



TRANSFER PUMPS WITH EX-PROOF MOTOR

Type	Flow rate at atmos. pressure (l/min)	Suction height (mWg)	Max. pressure (bar)
NF 1.100 EX	1.2	2.5	4
NF 1.300 EX	3	2.5	4

LABORATORY PUMPS

- Diaphragm pumps for laboratory applications
- Intelligent design
- High chemical resistance
- Reliable and maintenance-free
- Intuitive handling



LIQUIPORT

Pumps for industry and laboratory

TRANSFER PUMPS					
Type	Flow rate at atmos. pressure (l/min)	Suction height (mWg)	Pressure (bar)	Materials of head components	
				Head	Valves, Diaphragm
NF 100	0.2 – 1.3	3.0	1	PP, PVDF, PTFE	FFKM, PTFE
NF 1.100	0.2 – 1.3	3.0	4	PP, PVDF, PTFE	FFKM, PTFE
NF 300	0.5 – 3.0	3.0	1	PP, PVDF, PTFE	FFKM, PTFE
NF 1.300	0.5 – 3.0	3.0	4	PP, PVDF, PTFE	FFKM, PTFE



SIMDOS 02

The easy way to dose aggressive and neutral liquids

DOSING PUMP						
Type	Flow rate at atmos. pressure	Dosing range	Suction height (mWg)	Pressure (bar)	Materials of head components	
					Head	Valves, Diaphragm
FEM 1.02	30 µl/min – 20 ml/min	30 µl – 999 ml	2.0	6	PP, PVDF, PTFE, STAINLESS STEEL	FFKM, PTFE, EPDM



SIMDOS 10

The easy way to dose aggressive and neutral liquids

DOSING PUMP						
Type	Flow rate at atmos. pressure	Dosing range	Suction height (mWg)	Pressure (bar)	Materials of head components	
					Head	Valves, Diaphragm
FEM 1.10	1 – 100 ml/min	1 – 999 ml	3.0	6	PP, PVDF, PTFE, STAINLESS STEEL	FFKM, PTFE, EPDM

ACCESSORIES FOR OEM AND LABORATORY PUMPS

KNF offers a full range of accessories. The most common ones are listed below. For further parts, contact your local KNF partner or consult our accessory catalogue.

PRESSURE RELIEF VALVES				
Type	Max. flow rate with liquid (l/min)	Setting range (barg)	Material selection	
			Lower body	Diaphragm
FDV 30/31	3.0	0.5 – 2.5	PP, PVDF	EPDM, FKM, FFKM
FDV 1.30/1.31	3.0	2.0 – 6.5	PP, PVDF	EPDM, FKM, FFKM
FDV 300/301	12.0	0.8 – 2.5	PP, PVDF	EPDM, FKM, FFKM
FDV 1.300/1.301	12.0	2.0 – 6.5	PP, PVDF	EPDM, FKM, FFKM



This valve can be used for different purposes eg.: keeping the pressure constant, as a pressure safety valve or to prevent siphoning through the pump.

PULSATION DAMPERS				
Type	KNF pump type being used	Max. pressure (bar)	Material selection	
			Upper body	Diaphragm
FPD 06	NF 5 / NF 10 / FL 10 / FF 12 / FF 20 / NF 25 / NF 30 / NF 60 / NF 100 / FP 70	2	PP, PVDF	EPDM, FFKM
FPD 1.06	NF 1.5 / NF 1.25 / NF 1.30 / NF 1.60 / FP 150 / FP 1.150	6	PP, PVDF	EPDM, FFKM
FPD 10	NF 300 / NF 600 / FP 400	2	PP, PVDF	EPDM, FFKM
FPD 1.10	NF 1.100 / NF 1.300 / NF 1.600 / FP 1.400	6	PP, PVDF	EPDM, FFKM



Reduces pulsation in a liquid system

IN-LINE FILTERS				
Type	Material	Mesh opening (µm)	Max. flow rate with liquid (l/min)	Connectors
FS 60 T	PVDF	70	0.6	UNF 1/4" - 28
FS 60 X	PEEK	35	0.6	UNF 1/4" - 28
FS 25 T	PVDF	70	0.25	for tubes ID 3.2 or 4 mm
FS 25 X	PEEK	35	0.25	for tubes ID 3.2 or 4 mm



Prevents foreign objects from entering the liquid system

YOUR LOCAL PARTNER AROUND THE WORLD

KNF SALES ORGANIZATION

Australia KNF Regional Office
Moreland West VIC 3055
Tel. +61 3 9386 4959
info@knf.com.au
www.knf.com.au

Benelux Netherlands KNF Verder B.V.
NL3451 GG Vleuten
Tel. +31 30 677 92 40
info@knf-verder.nl
www.knf-verder.nl

Benelux Belgium und Luxemburg
KNF Verder N.V.
B-2630 Aartselaar
Tel. +32 3 871 96 24
info@knf.be
www.knf.be

China KNF Technology (Shanghai) Co., Ltd.
Shanghai 201203
Tel. +86 21 5109 9695
info.cn@knf.com
www.knf.com.cn

France KNF Neuberger SAS
F-68128 Village-Neuf
Tel. +33 389 70 35 00
info.fr@knf.com
www.knf.fr

Germany KNF Neuberger GmbH
D-79112 Freiburg
Tel. +49 7664 5909 0
info.de@knf.com
www.knf.de

India KNF Pumps + Systems (India) Pvt. Ltd.
Pimpale Nilakh, Pune 411 027
Tel. +91 82370 08923
+91 82370 13923
info.in@knf.com
www.knfpumps.in

Italy KNF Italia S.r.l.
I-20063 Cernusco s. Naviglio MI
Tel. +39 02 929 0491
info.it@knf.com
www.knf.it

Japan KNF Japan Co.Ltd.
Tokyo 104-0033
Tel. +81 3 3551 7931
info.jp@knf.com
www.knf.co.jp

Korea KNF Neuberger Ltd.
06174, Seoul
Tel. +82 2 959 0255
knf.kr@knf.com
www.knfkorea.com

Latin America KNF Neuberger, Inc.
Tel. +1 609 890 8600
knfusa@knf.com
www.knf.com/es

Morocco, Tunisia, Algeria
KNF Neuberger SAS
F-68128 Village-Neuf
Tel. +33 389 70 35 00
info.fr@knf.com
www.knf.fr

Singapore KNF Regional Office
Tel. +65 9722 1994
info@knf.com.sg
www.knf.com.sg

Sweden, Finland, Denmark, Norway
KNF Neuberger AB
SE-11743 Stockholm
Tel. +46 8 744 51 13
info.se@knf.com
www.knf.se

Switzerland KNF Neuberger AG
CH-8362 Balzerswil
Tel. +41 71 973 99 30
knf.ch@knf.com
www.knf.ch

UK, Ireland KNF Neuberger U.K., Ltd.
Witney, Oxfordshire OX28 4FA
Tel. +44 1993 77 83 73
info.uk@knf.com
www.knf.co.uk

USA, Canada KNF Neuberger, Inc.
Trenton, New Jersey 08691-1810
Tel. +1 609 890 8600
knfusa@knf.com
www.knfusa.com

KNF PRODUCT CENTERS

Gas Pumps KNF Neuberger GmbH
D-79112 Freiburg
info.ch@knf.com
www.knf.de

Micro Gas Pumps KNF Micro AG
CH-6260 Reiden
info.Micro@knf.com
www.knf-micro.ch

Liquid Pumps KNF Flodos AG
CH-6210 Sursee
info.flodos@knf.com
www.knf-flodos.ch